


















TEAVA PP

TEAVA PP Ø 32	TEAVA PP Ø 40	TEAVA PP Ø 50																		
																				
<table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th style="text-align: left;">DIAMETRU</th> </tr> </thead> <tbody> <tr><td>Ø 32-250mm</td></tr> <tr><td>Ø 32-500mm</td></tr> <tr><td>Ø 32-1000mm</td></tr> <tr><td>Ø 32-2000mm</td></tr> <tr><td>Ø 32-3000mm</td></tr> </tbody> </table>	DIAMETRU	Ø 32-250mm	Ø 32-500mm	Ø 32-1000mm	Ø 32-2000mm	Ø 32-3000mm	<table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th style="text-align: left;">DIAMETRU</th> </tr> </thead> <tbody> <tr><td>Ø 40-250mm</td></tr> <tr><td>Ø 40-500mm</td></tr> <tr><td>Ø 40-1000mm</td></tr> <tr><td>Ø 40-2000mm</td></tr> <tr><td>Ø 40-3000mm</td></tr> </tbody> </table>	DIAMETRU	Ø 40-250mm	Ø 40-500mm	Ø 40-1000mm	Ø 40-2000mm	Ø 40-3000mm	<table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th style="text-align: left;">DIAMETRU</th> </tr> </thead> <tbody> <tr><td>Ø 50-250mm</td></tr> <tr><td>Ø 50-500mm</td></tr> <tr><td>Ø 50-1000mm</td></tr> <tr><td>Ø 50-2000mm</td></tr> <tr><td>Ø 50-3000mm</td></tr> </tbody> </table>	DIAMETRU	Ø 50-250mm	Ø 50-500mm	Ø 50-1000mm	Ø 50-2000mm	Ø 50-3000mm
DIAMETRU																				
Ø 32-250mm																				
Ø 32-500mm																				
Ø 32-1000mm																				
Ø 32-2000mm																				
Ø 32-3000mm																				
DIAMETRU																				
Ø 40-250mm																				
Ø 40-500mm																				
Ø 40-1000mm																				
Ø 40-2000mm																				
Ø 40-3000mm																				
DIAMETRU																				
Ø 50-250mm																				
Ø 50-500mm																				
Ø 50-1000mm																				
Ø 50-2000mm																				
Ø 50-3000mm																				
TEAVA PP Ø 75	TEAVA PP Ø 110																			
																				
<table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th style="text-align: left;">DIAMETRU</th> </tr> </thead> <tbody> <tr><td>Ø 75-250mm</td></tr> <tr><td>Ø 75-500mm</td></tr> <tr><td>Ø 75-1000mm</td></tr> <tr><td>Ø 75-2000mm</td></tr> <tr><td>Ø 75-3000mm</td></tr> </tbody> </table>	DIAMETRU	Ø 75-250mm	Ø 75-500mm	Ø 75-1000mm	Ø 75-2000mm	Ø 75-3000mm	<table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th style="text-align: left;">DIAMETRU</th> </tr> </thead> <tbody> <tr><td>Ø 110-250mm</td></tr> <tr><td>Ø 110-500mm</td></tr> <tr><td>Ø 110-1000mm</td></tr> <tr><td>Ø 110-2000mm</td></tr> <tr><td>Ø 110-3000mm</td></tr> </tbody> </table>	DIAMETRU	Ø 110-250mm	Ø 110-500mm	Ø 110-1000mm	Ø 110-2000mm	Ø 110-3000mm							
DIAMETRU																				
Ø 75-250mm																				
Ø 75-500mm																				
Ø 75-1000mm																				
Ø 75-2000mm																				
Ø 75-3000mm																				
DIAMETRU																				
Ø 110-250mm																				
Ø 110-500mm																				
Ø 110-1000mm																				
Ø 110-2000mm																				
Ø 110-3000mm																				

FITINGURI PP

COT PP 15°	COT PP 30°	COT PP 45°																													
																															
<table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th style="text-align: left;">DIAMETRU</th> </tr> </thead> <tbody> <tr><td>Ø 32</td></tr> <tr><td>Ø 40</td></tr> <tr><td>Ø 50</td></tr> <tr><td>Ø 75</td></tr> <tr><td>Ø 110</td></tr> </tbody> </table>	DIAMETRU	Ø 32	Ø 40	Ø 50	Ø 75	Ø 110	<table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th style="text-align: left;">DIAMETRU</th> </tr> </thead> <tbody> <tr><td>Ø 32</td></tr> <tr><td>Ø 40</td></tr> <tr><td>Ø 50</td></tr> <tr><td>Ø 75</td></tr> <tr><td>Ø 110</td></tr> </tbody> </table>	DIAMETRU	Ø 32	Ø 40	Ø 50	Ø 75	Ø 110	<table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th style="text-align: left;">DIAMETRU</th> </tr> </thead> <tbody> <tr><td>Ø 32</td></tr> <tr><td>Ø 40</td></tr> <tr><td>Ø 50</td></tr> <tr><td>Ø 75</td></tr> <tr><td>Ø 110</td></tr> </tbody> </table>	DIAMETRU	Ø 32	Ø 40	Ø 50	Ø 75	Ø 110											
DIAMETRU																															
Ø 32																															
Ø 40																															
Ø 50																															
Ø 75																															
Ø 110																															
DIAMETRU																															
Ø 32																															
Ø 40																															
Ø 50																															
Ø 75																															
Ø 110																															
DIAMETRU																															
Ø 32																															
Ø 40																															
Ø 50																															
Ø 75																															
Ø 110																															
COT PP 67°	COT PP 87°	MUFA PP																													
																															
<table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th style="text-align: left;">DIAMETRU</th> </tr> </thead> <tbody> <tr><td>Ø 32</td></tr> <tr><td>Ø 40</td></tr> <tr><td>Ø 50</td></tr> <tr><td>Ø 75</td></tr> <tr><td>Ø 110</td></tr> </tbody> </table>	DIAMETRU	Ø 32	Ø 40	Ø 50	Ø 75	Ø 110	<table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th style="text-align: left;">DIAMETRU</th> </tr> </thead> <tbody> <tr><td>Ø 32</td></tr> <tr><td>Ø 40</td></tr> <tr><td>Ø 50</td></tr> <tr><td>Ø 75</td></tr> <tr><td>Ø 110</td></tr> </tbody> </table>	DIAMETRU	Ø 32	Ø 40	Ø 50	Ø 75	Ø 110	<table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th style="text-align: left;">DIAMETRU</th> </tr> </thead> <tbody> <tr><td>Ø 32</td></tr> <tr><td>Ø 40</td></tr> <tr><td>Ø 50</td></tr> <tr><td>Ø 75</td></tr> <tr><td>Ø 110</td></tr> </tbody> </table>	DIAMETRU	Ø 32	Ø 40	Ø 50	Ø 75	Ø 110											
DIAMETRU																															
Ø 32																															
Ø 40																															
Ø 50																															
Ø 75																															
Ø 110																															
DIAMETRU																															
Ø 32																															
Ø 40																															
Ø 50																															
Ø 75																															
Ø 110																															
DIAMETRU																															
Ø 32																															
Ø 40																															
Ø 50																															
Ø 75																															
Ø 110																															
RAMIFICATIE PP 67°	RAMIFICATIE PP 45°	RAMIFICATIE PP 87°																													
																															
<table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th style="text-align: left;">DIAMETRU</th> </tr> </thead> <tbody> <tr><td>ø 32/32*67°</td></tr> <tr><td>ø 40/40*67°</td></tr> <tr><td>ø 50/50*67°</td></tr> <tr><td>ø 75/75*67°</td></tr> <tr><td>ø 110/50*67°</td></tr> <tr><td>ø 110/110*67°</td></tr> </tbody> </table>	DIAMETRU	ø 32/32*67°	ø 40/40*67°	ø 50/50*67°	ø 75/75*67°	ø 110/50*67°	ø 110/110*67°	<table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th style="text-align: left;">DIAMETRU</th> </tr> </thead> <tbody> <tr><td>ø 32/32*45°</td></tr> <tr><td>ø 40/40*45°</td></tr> <tr><td>ø 50/40*45°</td></tr> <tr><td>ø 50/50*45°</td></tr> <tr><td>ø 75/50*45°</td></tr> <tr><td>ø 75/75*45°</td></tr> <tr><td>ø 110/40*45°</td></tr> <tr><td>ø 110/50*45°</td></tr> <tr><td>ø 110/75*45°</td></tr> <tr><td>ø 110/110*45°</td></tr> </tbody> </table>	DIAMETRU	ø 32/32*45°	ø 40/40*45°	ø 50/40*45°	ø 50/50*45°	ø 75/50*45°	ø 75/75*45°	ø 110/40*45°	ø 110/50*45°	ø 110/75*45°	ø 110/110*45°	<table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th style="text-align: left;">DIAMETRU</th> </tr> </thead> <tbody> <tr><td>ø 32/32*87°</td></tr> <tr><td>ø 40/40*87°</td></tr> <tr><td>ø 50/40*87°</td></tr> <tr><td>ø 50/50*87°</td></tr> <tr><td>ø 75/50*87°</td></tr> <tr><td>ø 75/75*87°</td></tr> <tr><td>ø 110/40*87°</td></tr> <tr><td>ø 110/50*87°</td></tr> <tr><td>ø 110/75*87°</td></tr> <tr><td>ø 110/110*87°</td></tr> </tbody> </table>	DIAMETRU	ø 32/32*87°	ø 40/40*87°	ø 50/40*87°	ø 50/50*87°	ø 75/50*87°	ø 75/75*87°	ø 110/40*87°	ø 110/50*87°	ø 110/75*87°	ø 110/110*87°
DIAMETRU																															
ø 32/32*67°																															
ø 40/40*67°																															
ø 50/50*67°																															
ø 75/75*67°																															
ø 110/50*67°																															
ø 110/110*67°																															
DIAMETRU																															
ø 32/32*45°																															
ø 40/40*45°																															
ø 50/40*45°																															
ø 50/50*45°																															
ø 75/50*45°																															
ø 75/75*45°																															
ø 110/40*45°																															
ø 110/50*45°																															
ø 110/75*45°																															
ø 110/110*45°																															
DIAMETRU																															
ø 32/32*87°																															
ø 40/40*87°																															
ø 50/40*87°																															
ø 50/50*87°																															
ø 75/50*87°																															
ø 75/75*87°																															
ø 110/40*87°																															
ø 110/50*87°																															
ø 110/75*87°																															
ø 110/110*87°																															

RAMIFICATIE REDUSA PP 45°		RAMIFICATIE REDUSA PP 67°		RAMIFICATIE REDUSA PP 87°	
	DIAMETRU		DIAMETRU		DIAMETRU
	ø 40/32*45°		ø 40/32*67°		ø 50/40*87°
	ø 50/40*45°		ø 50/32*67°		ø 75/50*87°
	ø 75/50*45°		ø 50/40*67°		ø 110/40*87°
	ø 110/40*45°		ø 75/50*67°		ø 110/50*87°
	ø 110/50*45°		ø 110/40*67°		ø 110/75*87°
ø 110/75*45°	ø 110/50*67°				
ø 110/75*45°	ø 110/75*67°				
REDUCTIE PP		PIESA INSPECTIE PP		DOP PP	
	DIAMETRU		DIAMETRU		DIAMETRU
	ø 40-32		ø 50		ø32
	ø 50-32		ø 75		ø40
	ø 50-40		ø110		ø50
	ø 75-50		ø75		
	ø 110-50		ø110		
	ø 110-75				
CACIULA VENTILATIE PP		RAMIFICATIE DUBLA PP			
	DIAMETRU		DIAMETRU		
	ø 50		ø 110/50*45°		
	ø 75		ø 110/50*87°		
	ø110		ø 110/110/110*45°		
			ø 110/110/110*87°		